Clamp Gaskets

Specifications

• PSI Service Ratings for the sanitary clamps DO NOT APPLY to connections (1" and above) using any PTFE gaskets, due to the potential for cold flow under normal operating conditions. PTFE gaskets, when used with any clamp, are likely to leak at pressures far below the published service ratings. This restriction does not apply to the fractionally sized 1/2" and 3/4" connections, due to their recessed, fully contained design.

Approval

• Gasket material approved by (3A), USDA and complies with FDA's 21CFR177.2600 and 1550









Flanged - type 2



Type 1 - Standard 1" and larger



Type 1 - Standard 1/2" - 3/4"







Type 1 - Standard ", 1" and larger



Type 1 - Standard 1/2" - 3/4"



Type 1 - Standard 1" and larger



Type 1 - Standard 1/2" - 3/4"

Standard - type 1 **Clamp Gaskets - Black**

Feature Color code: one red dot

Approval

• Meets 21CFR 177.2600

Size	Nitrile Rubber Part #
1/2"	42MP-U50
3/4"	42MP-U75
1"	40MP-U100
1-1/2"	40MP-U150
2"	40MP-U200
2-1/2"	40MP-U250
3"	40MP-U300
4"	40MP-U400
5"	40MP-U500
6"	40MP-U600
8"	40MP-U800

Clamp Gaskets - White

Feature	Size	Nitrile Rubber Part #
	5126	Nitile Rubbel Fait #
 Color code: one red dot 	1/2"	42MP-UW50
Approval	3/4"	42MP-UW75
ApprovalMeets 21CFR 177.2600	1"	40MP-UW100
Weets 2101 11 11 . 2000	1-1/2"	40MP-UW150
	2"	40MP-UW200
	2-1/2"	40MP-UW250
	3"	40MP-UW300
	4"	40MP-UW400
	6"	40MP-UW600

Clamp Gaskets - Black

Features	Size	EPDM Part #
Color code: three green dotsPeroxide cured	1/2"	42MP-E50
	3/4"	42MP-E75
Approvals • Meets 21CFR 177.2600 • Passed U.S.P. Class VI Cytotoxicity testing	1"	40MP-E100
	1-1/2"	40MP-E150
	2"	40MP-E200
	2-1/2"	40MP-E250
	3"	40MP-E300
	4"	40MP-E400
	5"	40MP-E500
	6"	40MP-E600

Visit dixonvalve.com for sizing charts.